

Specification Sheet

Part Number: 596-00655

Made with UV-stable inks and materials for durability and weather resistance.

Reflective properties to meet applicable NEC code requirements for reflective identification.

Supplied with an aggressive adhesive to ensure long life.

|                                |  |
|--------------------------------|--|
| NOMINAL OPERATING AC VOLTAGE   |  |
| NOMINAL OPERATING AC FREQUENCY |  |
| MAXIMUM AC POWER               |  |
| MAXIMUM AC CURRENT             |  |
| MAX OVERCURRENT DEVICE RATING  |  |
| FOR AC MODULE PROTECTION       |  |

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Solar Label, Printable, AC MODULE, 4.0" x 2.0", PET, Red, 50/roll

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                               |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 596-00655                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Type                | AC2011-1                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Color               | Red (RD)                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Product Description | Designed in a one-across landscape format to fit into the compact TT130SMC thermal transfer printer, these labels allow for code-compliant marking of variable information including disconnecting means, breaker series and voltage data. Made with cross-laminated UV stable materials, labels are ideal for use in solar installation applications. Use with the TT130SMC or any HellermannTyton thermal transfer printer. |

|                                |                                                                            |
|--------------------------------|----------------------------------------------------------------------------|
| Short Description              | Solar Label, Printable, AC MODULE, 4.0" x 2.0", PET, Red, 50/roll          |
| Global Part Name               | AC2011-1-840/281-RD                                                        |
| Width W (Imperial)             | 2.0                                                                        |
| Width W (Metric)               | 50.8                                                                       |
| Thickness T (Metric)           | 64.0                                                                       |
| Height H (Imperial)            | 4.0                                                                        |
| Height H (Metric)              | 101.6                                                                      |
| Material                       | Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281) |
| Material Shortcut              | 840/281                                                                    |
| Adhesive                       | Acrylic                                                                    |
| Halogen Free                   | No                                                                         |
| UV Resistant (Yes/No)          | Yes                                                                        |
| Use Conditions                 | For Indoor and Outdoor Use                                                 |
| Adhesive Operating Temperature | -40°F to +302°F (-40°C to +150°C)                                          |

|                       |                                   |
|-----------------------|-----------------------------------|
| Operating Temperature | -40°F to +302°F (-40°C to +150°C) |
|-----------------------|-----------------------------------|

|                              |     |
|------------------------------|-----|
| Reach Compliant (Article 33) | Yes |
|------------------------------|-----|

|                |     |
|----------------|-----|
| ROHS Compliant | Yes |
|----------------|-----|

|                             |        |
|-----------------------------|--------|
| Certification/Specification | UL 969 |
|-----------------------------|--------|

|                    |     |
|--------------------|-----|
| UL Recognized (US) | Yes |
|--------------------|-----|

|                             |    |
|-----------------------------|----|
| Package Quantity (Imperial) | 50 |
|-----------------------------|----|

|                           |    |
|---------------------------|----|
| Package Quantity (Metric) | 50 |
|---------------------------|----|

|                |            |
|----------------|------------|
| Customs Number | 3919102055 |
|----------------|------------|

|                   |   |
|-------------------|---|
| Labels per Column | 1 |
|-------------------|---|

|                |   |
|----------------|---|
| Labels per Row | 1 |
|----------------|---|

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)