

Specification Sheet

Part Number: 596-00495

Pre-Printed Vinyl Solar Labels are made with UV-stable inks and materials for durability and weather resistance.

Supplied with an aggressive adhesive to ensure long life.

Meets NEC® & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Pre-printed labels offer significant time and cost savings over high-priced plastic engraved phenolic placards and the lead time of purchased markers.



Solar Label, WARNING DUAL POWER SOURCE...SYSTEM, 4.125" x .75", VL, Orange, 50/roll

Article Number 596-00495

Type WDPSLBL

Color Orange (OG)

Quantity Per pack

Product Description HellermannTyton pre-printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description Solar Label, WARNING DUAL POWER SOURCE...SYSTEM, 4.125" x .75", VL, Orange, 50/roll

Global Part Name

WDPSLBL-443/281-OG

Local Order Number 2

Cross Reference = 10 per pack: 596-00665; Metal Solar Placard 5
pack: 596-00833

Width W (Imperial)

4.125

Width W (Metric)

104.6

Thickness T (Imperial)

0.0025

Thickness T (Metric)

64.0

Height H (Imperial)

0.75

Height H (Metric)

19.05

Material

Type 443/281, UV stabilized, flexible white vinyl with clear polyester
laminate (443/281)

Material Shortcut

443/281

Adhesive

Acrylic

Halogen Free

No

UV Resistant (Yes/No)

Yes

Use Conditions

For Indoor and Outdoor Use

Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2020 NEC2017 NEC2023 NEC2014
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)