

Specification Sheet


Part Number: 596-01005

Made with UV-stable inks and materials for durability and weather resistance

Polyester is resistant to chemicals and solvents and will remain legible in dirty environments

High abrasion and scuff resistance for high-performance labeling

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections



Solar Label, Printable, ENERGY STORAGE SYSTEM RATING LABEL, 3.75" X 2.12", PET, Red, 10/pkg

Article Number	596-01005
Type	ESS202010
Color	Red (RD)
Quantity Per	pack

Product Description	HellermannTyton makes it easier than ever for solar installers to meet PV labeling codes. Solar Label Convenience Packs allow installers to quickly and economically purchase high quality preprinted NEC code-compliant solar installation labels. Packaged in 10-count quantities to meet the needs of smaller scale solar installations and independent contractors, Solar Label Convenience Packs are available in HellermannTyton's most popular preprinted NEC code-compliant solar label formats. Each Solar Label Convenience Pack contains 10 solar installation labels. Choose from a variety of regular and reflective preprinted labels. For enhanced durability, clear laminate overlay labels are also available in a convenience pack.
Short Description	Solar Label, Printable, ENERGY STORAGE SYSTEM RATING LABEL, 3.75" X 2.12", PET, Red, 10/pkg
Global Part Name	ESS202010-840/281-RD
Width W (Imperial)	3.75
Width W (Metric)	92.25
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	2.1
Height H (Metric)	53.34
Width of Liner (Metric)	98.29
Width of Liner (Imperial)	3.87

Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017 CSA 66956 UL 969 NEC2023
UL Recognized (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3919905060
Labels per Column	1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)