

# Product data sheet

## Characteristics

# APCRBC110

## APC Replacement Battery Cartridge #110 with 2 Year Warranty



### Overview

Lead time	Usually in Stock
-----------	------------------



### Main

Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide

### Physical

Color	Black
Height	4.13 in (10.5 cm)
Width	5.94 in (15.1 cm)
Depth	2.56 in (6.5 cm)
Net Weight	5.51 lb(US) (2.5 kg)
Mounting Mode	Not rack-mountable
USB compatible	No

### Output

Battery Capacity	7.0 Ah
------------------	--------

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

### Batteries & Runtime

Included Battery Modules	0
Device mounting	Enclosed battery cabinet
Battery Voltage	12 V
RBC Quantity	1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

GTIN	731304248217
Package weight(Lbs)	5.20 lb(US) (2.36 kg)

## Packing Units

Package 1 Height	3.31 in (8.4 cm)
Package 1 width	6.89 in (17.5 cm)
Package 1 Length	8.27 in (21 cm)
Number of Units in Package 3	240

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------