



Overview

| | |
|--------------|---|
| Presentation | Extended run power protection for servers, networks, and telecommunications |
| Lead time | Usually in Stock |

Main

| | |
|---------------------|-------------------|
| Number of rack unit | 2U |
| Number of cables | 1.0 |
| Battery Type | Lead-Acid battery |

Physical

| | |
|----------------|-------------------------|
| Color | Beige |
| Height | 3.27 in (8.3 cm) |
| Width | 8.50 in (21.6 cm) |
| Depth | 21.50 in (54.6 cm) |
| Net Weight | 49.10 lb(US) (22.27 kg) |
| Mounting Mode | Not rack-mountable |
| USB compatible | No |

Environmental

| | |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C) |
| Operating altitude | 0...10000 ft |
| Relative Humidity | 0...95 % |
| Ambient Air Temperature for Storage | 5...113 °F (-15...45 °C) |
| Storage altitude | 0...50000 ft (0.00...15240.00 m) |
| Storage Relative Humidity | 0...95 % |

Batteries & Runtime

| | |
|--------------------------|----------------------------|
| Battery Placement | Internal Battery |
| Battery Slots Empty | 0 |
| Included Battery Modules | 0 |
| Device mounting | Enclosed battery cartridge |
| RBC Quantity | 1 |

Ordering and shipping details

| | |
|---------------------|-------------------------|
| GTIN | 731304016908 |
| Package weight(Lbs) | 52.60 lb(US) (23.86 kg) |

Packing Units

| | |
|------------------------------|--------------------|
| Package 1 Height | 9.76 in (24.8 cm) |
| Package 1 width | 14.02 in (35.6 cm) |
| Package 1 Length | 25.98 in (66 cm) |
| Number of Units in Package 3 | 12 |

Offer Sustainability

| | |
|---------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|--|
| Warranty | 2 years repair or replace, optional on-site warranties available, optional extended warranties available |
|----------|--|