



## Main

|                             |                          |
|-----------------------------|--------------------------|
| Range of Product            | Harmony 9001B            |
| Product or Component Type   | Complete control station |
| Device short name           | 9001BG                   |
| Control station application | Three functions          |
| Colour of base of enclosure | Grey                     |

## Complementary

|                                |                                      |
|--------------------------------|--------------------------------------|
| Material                       | Cast zinc                            |
| Marking                        | CE                                   |
| Type of operator               | momentary                            |
| Control station composition    | 3 push-buttons, white START-JOG-STOP |
| Contacts type and composition  | 2 NO + 3 NC                          |
| Mechanical durability          | 5000000 cycles                       |
| [Ie] rated operational current | 5 A 600 V, AC                        |
| Device mounting                | Surface                              |
| Type of Installation           | Indoor                               |

## Environment

|                                       |                                                             |
|---------------------------------------|-------------------------------------------------------------|
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                  |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C)                                  |
| NEMA degree of protection             | NEMA 1                                                      |
| Product Certifications                | UL listed file E42259 CCN NKCR<br>CSA LR25490 class 3211 03 |

## Ordering and shipping details

|                   |                                |
|-------------------|--------------------------------|
| Category          | 21421-9001 B (NOT BW70 - BW80) |
| Discount Schedule | CS1                            |
| GTIN              | 785901794240                   |
| Returnability     | No                             |
| Country of origin | MX                             |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 12.70 in (32.258 cm) |
| Package 1 Width              | 5.00 in (12.7 cm)    |
| Package 1 Length             | 32.26 in (81.935 cm) |
| Package 1 Weight             | 16.00 oz (453.592 g) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                      |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                         |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Approximate Dimensions

