

Product data sheet

Characteristics

9001SKR24G

Push-button head, Harmony 9001SK, plastic, mushroom 35mm, green, 30mm, spring return



Main

Range of Product	Harmony 9001SK
Product or Component Type	Head for push-button
Device short name	9001SK
Operator additional information	Screw-on plastic with set screw

Complementary

Bezel material	Plastic
Shape of signaling unit head	Round
Mechanical durability	5000000 cycles
Device presentation	Basic element
Cap/operator or lens colour	Green
Operator profile	Mushroom Ø 35 mm
Type of operator	Spring return
Contacts type and composition	Without contact block
Size	30 mm

Environment

Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Overvoltage category	Class II IEC 61140
IP degree of protection	IP66
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03
Vibration resistance	7 gn 2...500 Hz IEC 60068-2-6

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	785901042174
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.62 in (19.355 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	19.35 in (49.161 cm)
Package 1 Weight	8.00 oz (226.796 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------