

# Product data sheet

## Characteristics

# ABFM32H150

## cabled connector - 1.5 m - for Modicon Quantum



### Main

Range of Product	Modicon Quantum
Accessory / separate part designation	Cabled connector
Accessory / Separate Part Type	Connector
Accessory / separate part category	Connection accessories
Accessory / separate part destination	Modicon Quantum PLC
Number of Channels	32

### Complementary

Cable length	4.92 ft (1.5 m)
Type of signal	Relay I/O
Electrical Connection	2 connectors
Connector Type	HE10
Number of ways	20 ways
Wire section	0.00 in <sup>2</sup> (0.324 mm <sup>2</sup> )
AWG Gauge	AWG 22
Channel splitting	2 x 16
Net Weight	1.43 lb(US) (0.65 kg)

### Ordering and shipping details

Category	22375-INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	3389110705324
Returnability	No

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	11.42 in (29.000 cm)
Package 1 Length	8.31 in (21.100 cm)
Package 1 Weight	28.71 oz (814.000 g)
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	16.72 lb(US) (7.585 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	32
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	87.21 lb(US) (39.556 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------