

SQR44203WH

Socket-outlet, X Series, 20A, decorator, tamper resistant, commercial, white, matte finish, 30 pcs



Main

Range	Square D X Series
Product or Component Type	Socket-outlet
Device Application	Power supply
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series
Outlet poles configuration	2P + E
Outlet standard	NEMA
Socket additional information	Tamper resistant

Complementary

Body type	Decorator
Number of modules	1
Socket number	2
Number of gangs	1 gang
[Ie] rated operational current AC	20 A
[Ue] rated operational voltage	125 V
Network type	AC
Network Frequency	60 Hz
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic strap Metal fixing frame
Color	White
Surface Finish	Matte
Connections - terminals	Phase and neutral 4 screw terminal AWG 12...AWG10) copper Earth 1 screw terminal copper
Earth circuit	Self earthing
Width	1.54 in (39 mm)
Height	4.06 in (103 mm)
Depth	1.22 in (31 mm)
Quantity per Set	30 pieces

Environment

Product Certifications	cULus
Standards	UL 498 NEMA 5-20R

Ordering and shipping details

Category	09931-WD ADVANCED DEVICES
Discount Schedule	DE9
GTIN	785901544098
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.06 in (2.69 cm)
Package 1 Width	1.31 in (3.32 cm)
Package 1 Length	4.06 in (10.3 cm)
Package 1 Weight	0.95 oz (26.9 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	30
Package 2 Height	2.83 in (7.2 cm)
Package 2 Width	12.52 in (31.8 cm)
Package 2 Length	15.20 in (38.6 cm)
Package 2 Weight	5.08 lb(US) (2.302 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	180
Package 3 Height	14.17 in (36.0 cm)
Package 3 Width	12.91 in (32.8 cm)
Package 3 Length	15.94 in (40.5 cm)
Package 3 Weight	37.92 lb(US) (17.2 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	2 years
----------	---------