

Product data sheet

Specifications



Pump Panel, NEMA Type S, Well Guard, Size 2, 45A, 5kA SCCR, 30HP, 60A Class H and K fuse clip, Motor Logic SSOLR, 440/480VAC 50/60Hz coil, NEMA 3R

8940SSD4030

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Well-Guard Control
Type	class 8940 type SS
Device Application	Pumping

Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	45 A
Number of Poles	3
Horsepower Rating	30 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	60 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	2
Height	39.06 in (992 mm)
Width	15.2 in (385 mm)
Depth	9.7 in (246 mm)

Environment

NEMA Rating	NEMA 3R
-------------	---------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure type	Rainproof enclosure indoor/outdoor
Product Certifications	UL Listed NEMA

Ordering and shipping details

Category	US10CP121388
Discount Schedule	0CP1
GTIN	785901011767
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	9.80 in (24.892 cm)
Package 1 Width	17.50 in (44.45 cm)
Package 1 Length	36.60 in (92.964 cm)
Package weight(Lbs)	61.000 lb(US) (27.669 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	5
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	305.27 lb(US) (138.47 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Not compliant
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

 Repack and remanufacture	
Take-back	No