

Product data sheet

Characteristics

NBES0303

NetBotz Door Switch Sensors (2) for an APC Rack - 12 ft.



Overview

Presentation	Universal Sensor that monitors access to NetShelter SX Enclosures.
Lead time	Usually Ships within 2 Weeks

Main

Provided Equipment	Cable ties
Product Compatibility	4 - 20mA Sensor Rack Sensor Pod 150 Room Sensor Pod 155 Sensor Pod 120 NetBotz USB Camera Pod Pelco IP110-CHV9

General

Display Resolution	Up to 640x480
External Sensor Connection Type	Alarm Beacon 1 PS2 mini-DIN
APC Universal Sensors Supported	Door contact Humidity Smoke Temperature
Number of Universal Sensor Ports	2
Number of Sensor Pods Supported	0
Number of Universal Sensors Supported	0
Sensor Humidity Range	10...90 % +/- 5 % non-condensing RH
Number of Cameras Supported	4 for Networked 4
Sensor Temperature Range	1.6...48.8 °C: +/- 1 °C 35...120 °F:

Physical

Height	0.75 in (1.9 cm)
Width	5.75 in (14.6 cm)
Depth	7.36 in (18.7 cm)
Net Weight	0.82 lb(US) (0.37 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Output

Number of port	0
----------------	---

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Ordering and shipping details

GTIN	731304262855
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.89 in (4.8 cm)
Package 1 Width	9.13 in (23.2 cm)
Package 1 Length	6.46 in (16.4 cm)
Package 1 Weight	1.08 lb(US) (0.489 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant  EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------