

# Product data sheet

## Characteristics

# 9001KR24BH6

Push-button, Harmony 9001K, metal, mushroom 35mm, black, 30mm, spring return, 1 NC



### Main

|                                 |                                 |
|---------------------------------|---------------------------------|
| Range of Product                | Harmony 9001K                   |
| Product or Component Type       | Push-button                     |
| Device short name               | K                               |
| Type of operator                | Spring return                   |
| Operator profile                | Black mushroom Ø 35 mm          |
| Operator additional information | Screw-on plastic with set screw |

### Complementary

|                                |                            |
|--------------------------------|----------------------------|
| Bezel material                 | Metal                      |
| Mounting diameter              | 1.18 in (30 mm)            |
| Light source                   | without                    |
| Light source                   | Without                    |
| Light block supply             | Without supply             |
| Contacts type and composition  | 1 NC                       |
| Connections - terminals        | Screw clamp terminals      |
| Operating position             | Any position               |
| [Ie] rated operational current | 10 A, AC-15<br>10 A, DC-13 |
| Contact operation              | Standard                   |
| Device presentation            | Complete product           |
| Cap/operator or lens colour    | Black                      |
| Operator profile               | Mushroom Ø 35 mm           |
| Type of operator               | Spring return              |
| Size                           | 30 mm                      |

### Environment

|                           |  |
|---------------------------|--|
| Product Certifications    | CSA LR 25490 class 3211 03<br>UL listed file E42259 CCN NKCR<br>NEMA<br>CE |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13  |

### Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1                         |
| GTIN              | 785901345954                |
| Returnability     | No                          |
| Country of origin | MX                          |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 11.43 in (29.032 cm) |
| Package 1 Width              | 4.50 in (11.43 cm)   |
| Package 1 Length             | 29.03 in (73.742 cm) |
| Package 1 Weight             | 8.00 oz (226.796 g)  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           |  <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes   |
| RoHS exemption information |  Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|