

# Product data sheet

## Characteristics

# XBTZG9774

connecting cable, Harmony XBT GT, 5m direct connection cable, 1 male connector mini DIN/SUB-D9



### Main

Range of Product	Harmony XBT
Accessory / separate part category	Connection accessories
Product or Component Type	Connecting cable
Accessory / Separate Part Type	Connecting cable
Accessory / separate part designation	Direct connection cable
Accessory / separate part destination	Direct connection of XBT terminal to Mitsubishi Melsec PLC

### Complementary

Product Compatibility	XBTGT2... XBTOT... XBTGT5... XBTGK.... XBTGT7340 XBTGTW... XBTGT6... XBTGT4...
Range Compatibility	Mitsubishi Q CPU Harmony HMI GTO
Cable length	16.40 ft (5 m)
Electrical connection	1 male connector mini DIN 1 male connector SUB-D 9
Communication Port Protocol	Q CPU (SIO)
Physical interface	RS232C

### Ordering and shipping details

Category	22569-MAGELIS XBT-GT (AND XBT-G)
Discount Schedule	MC2
GTIN	3595863885590
Returnability	No
Country of origin	JP

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	6.89 in (17.5 cm)
Package 1 Length	10.24 in (26.0 cm)
Package 1 Weight	10.83 oz (307.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.65 lb(US) (1.654 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------