

# Product data sheet

Specifications



PC box IP66 IK08 RAL7035  
Int.H225W175D100  
Ext.H241W191D128 Transp.cover  
H20

NSYTBP241910T

## Main

Range	PanelSeT
Product name	PanelSeT TBP
Device application	Multi-purpose
Category	Industrial box
Height	241 mm
Width	194 mm
Depth	107 mm
Internal height	225 mm
Internal width	175 mm
Internal depth	100 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	Low transparent cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

## Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035) Transparent
Standards	UL 508 A IEC 62208
Product certifications	TÜV UL
Electrical insulation class	Class II
Mounting location	Outdoor (with canopy or shelter and anticondensation valve)
Product weight	0.72 kg

## Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
-------------------------	------------------------------

IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Operating temperature	-25...80 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.000 cm
Package 1 Width	20.000 cm
Package 1 Length	25.500 cm
Package 1 Weight	800.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	9
Package 2 Height	40.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	8.420 kg
Unit Type of Package 3	P12
Number of Units in Package 3	108
Package 3 Height	135.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	114.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint 7

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard No

Packaging without single use plastic No

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation [REACH Declaration](#)

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back No

## Technical Illustration

## Dimensions




Image of product in real life situation

