

Product data sheet

Characteristics

APCRBC88

APC Replacement Battery Cartridge #88 with 2 Year Warranty



Overview

| | |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|



Main

| | |
|--------------------|--|
| Battery Type | Lead-Acid battery |
| Provided Equipment | All required connectors Battery recycling guide Installation guide Reusable packaging |
| | |
| | |
| | |

Physical

| | |
|---------------|-------------------------|
| Height | 1.50 in (3.8 cm) |
| Width | 8.15 in (20.7 cm) |
| Depth | 18.90 in (48 cm) |
| Net Weight | 23.04 lb(US) (10.45 kg) |
| Mounting Mode | Not rack-mountable |

Environmental

| | |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C) |
| Operating altitude | 0...10000 ft |
| Relative Humidity | 0...95 % |
| Ambient Air Temperature for Storage | 32...104 °F (0...40 °C) |
| Storage altitude | 0...10000 ft (0.00...3048.00 m) |
| Storage Relative Humidity | 0...95 % |

Batteries & Runtime

| | |
|--------------------------|----------------------------|
| Battery Placement | Internal Battery |
| Battery Slots Empty | 0 |
| Included Battery Modules | 0 |
| Device mounting | Enclosed battery cartridge |
| RBC Quantity | 1 |

Ordering and shipping details

| | |
|---------------------|-------------------------|
| GTIN | 731304300038 |
| Package weight(Lbs) | 26.06 lb(US) (11.82 kg) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------|--------------------|
| Package 1 Height | 7.13 in (18.1 cm) |
| Package 1 width | 12.87 in (32.7 cm) |
| Package 1 Length | 23.74 in (60.3 cm) |

Offer Sustainability

| | |
|---------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|