



## Overview

|              |                                                                                                                                                                                    |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | The NetBotz Room Monitor 755 provides integrated surveillance, sensing, access control, and advanced alerting for IT environments of all sizes where IT rack space is unavailable. |
| Lead time    | Usually in Stock                                                                                                                                                                   |

## General

|                                  |                                                                                                         |
|----------------------------------|---------------------------------------------------------------------------------------------------------|
| Camera Frame Rate                | Up to 30fps                                                                                             |
| APC Universal Sensors Supported  | 0-5V<br>Door contact<br>Dry Contact<br>Fluid Spot Leak<br>Humidity<br>Smoke<br>Temperature<br>Vibration |
| Number of Universal Sensor Ports | 4                                                                                                       |

## Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Black                 |
| Height              | 5.51 in (14.0 cm)     |
| Width               | 9.61 in (24.4 cm)     |
| Depth               | 3.58 in (9.1 cm)      |
| Net Weight          | 3.44 lb(US) (1.56 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...113 °F (0...45 °C)          |
| Operating altitude                    | 0...9842.52 ft (0...3000 m)      |
| Ambient Air Temperature for Storage   | 5...149 °F (-15...65 °C)         |
| Storage altitude                      | 0.00...49212.60 ft (0...15000 m) |

## Communications & Management

|                            |                   |
|----------------------------|-------------------|
| Communication Network Type | 10/100/1000BASE-T |
|----------------------------|-------------------|

## Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| GTIN                | 731304347521          |
| Package weight(Lbs) | 8.20 lb(US) (3.72 kg) |

## Packing Units

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 4.76 in (12.1 cm)  |
| Package 1 width  | 20.98 in (53.3 cm) |
| Package 1 Length | 12.52 in (31.8 cm) |

## Offer Sustainability

|                   |                                                                                                                              |
|-------------------|------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive | Under investigation                                                                                                          |
| WEEE              | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |