

# Product data sheet

Specifications



Flush mounting kit, Harmony XB4, metal, black, for selector switch and illuminated push button 22mm

ZB4BZ022

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range of Product	Harmony XB4
Product or Component Type	Flush mounting kit
Accessory / separate part category	Mounting and fixing accessory
Accessory / separate part destination	Selector switch high bezel high guard Illuminated push-button high bezel high guard

## Complementary

Product Compatibility	ZB4BK ZB4BD.8 ZB4BD ZB4BD.9 ZB4BJ ZB4BH..3 ZB4BA.6 ZB4BW
Surface Finish	Chromium plated
IP degree of protection	IP66 IEC 60529 front face) IP69 IEC 60529 front face) IP69K DIN 40050-9 front face)
IK degree of protection	IK06 conforming to IEC 50102
Mounting diameter	1.2 in (30.5 mm)
Quantity per Set	Set of 1

## Ordering and shipping details

Category	US1CP1018079
Discount Schedule	CP10
GTIN	3606485440217
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.77 in (4.500 cm)
Package 1 Width	2.05 in (5.200 cm)
Package 1 Length	2.17 in (5.500 cm)
Package weight(Lbs)	1.164 oz (33.000 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Unit Type of Package 2</b>	S02
<b>Number of Units in Package 2</b>	80
<b>Package 2 Height</b>	5.91 in (15.000 cm)
<b>Package 2 Width</b>	11.81 in (30.000 cm)
<b>Package 2 Length</b>	15.75 in (40.000 cm)
<b>Package 2 Weight</b>	6.510 lb(US) (2.953 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
<a href="#">EU RoHS Directive</a>	Compliant

## Use Again

### Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.


## Dimensions Drawings

Dimensions with Flush Mounting Kit

e : Clamping thickness : 1.2 to 2.8 mm / 0.05 to 0.11 in.


(1) Additional row of contacts or double contact

## Mounting and Clearance

Panel Cut-Out and Mounting

## Technical Illustration

## Dimensions



## Offer Marketing Illustration

## Product benefits / Features

## Technical Benefits

## Harmony XB4

Conformity with IEC, UL, CSA, CCC EAC, and JIS standards, as well as CE marking and marine approvals

Up to IP66, 67, 69, 69K, and type 4X protection ratings

High vibration resistance with shake-proof terminal screws

Operating temperature from -40°C to 70°C

Shock protection level up to IK06

Secure switching of inductive or heavy DC loads directly – 100 000 operations at 10A, 24V dc



## Offer Marketing Illustration

## Product benefits / Features




Image of product / Alternate images

Alternative

---

