

SQR55241GY

USB charger + socket-outlet, X Series,
20A socket, 4.8A USB A/A, duplex, tamper
resistant, gray, matte finish



Main

Range	Square D X Series
Product or Component Type	USB charger + socket-outlet
Aesthetic name	X Series
Color	Gray

Complementary

Device Application	Power supply
Device presentation	Mechanism with fixing frame
Integrated connection type	2 socket-outlet 20 A 2 USB type A 2.4 A
Outlet poles configuration	2 x 2P + E
Outlet standard	NEMA
Socket additional information	Tamper resistant
Number of modules	1
[Ue] rated operational voltage	125 V
Network type	AC
Network Frequency	60 Hz
Number of gangs	1 gang
Device mounting	Flush
Mounting Mode	By screws
Material	Plastic strap Metal fixing frame
Surface Finish	Matte
Connections - terminals	Phase and neutral 2 screw terminal Earth 1 screw terminal
Earth circuit	Self earthing
Height	4.06 in (103 mm)
Width	1.73 in (44 mm)
Depth	1.73 in (44 mm)
Quantity per Set	1 piece

Environment

Product Certifications	cULus
Standards	UL 498 UL 1310 FCC Part 15 class B ICES-003

Ordering and shipping details

Category	09931-WD ADVANCED DEVICES
Discount Schedule	DE9
GTIN	785901546825
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.17 in (10.6 cm)
Package 1 Width	2.13 in (5.4 cm)
Package 1 Length	2.17 in (5.5 cm)
Package 1 Weight	5.36 oz (152.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.45 in (11.3 cm)
Package 2 Width	4.61 in (11.7 cm)
Package 2 Length	11.02 in (28.0 cm)
Package 2 Weight	3.62 lb(US) (1.644 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	1920
Package 3 Height	47.24 in (120.0 cm)
Package 3 Width	39.37 in (100.0 cm)
Package 3 Length	47.24 in (120.0 cm)
Package 3 Weight	834.78 lb(US) (378.648 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	2 years
----------	---------