

Product data sheet

Specifications



Complete push button, Harmony XAP, Pushbutton XB2B, diameter Ø22 mm, 600 VAC, 10 A

XB2BN411

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XAP
Product or Component Type	Complete push-button
Device short name	XB2B
Mounting diameter	0.9 in (22 mm)

Environment

Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)

Ordering and shipping details

Category	US10CS222461
Discount Schedule	0CS2
GTIN	3389110675467
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.57 in (4.000 cm)
Package 1 Width	1.57 in (4.000 cm)
Package 1 Length	2.95 in (7.500 cm)
Package weight(Lbs)	3.633 oz (103.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	90
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	20.988 lb(US) (9.520 kg)
Unit Type of Package 3	P06

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number of Units in Package 3	1440
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	353.445 lb(US) (160.320 kg)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **1**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **No**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

California proposition 65 **WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

Use Again

Repack and remanufacture

Circularity Profile **No need of specific recycling operations**

Take-back **No**

[WEEE Label](#) **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.**

Offer Marketing Illustration

Product benefits / Features

Features

Easy Harmony XB2



-  Metal bezels with metal fixing collars for impact endurance
-  Designed to be used in numerous control and signaling applications
-  Metal screws for secure fix, grounding contact to the panel and anti-rotation
-  Simple modular design facilitates post installation servicing, modification and adaption of machines by non-specialists
-  Available in sub-assemblies for easy mix and match of functionalities

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Easy Harmony XB2

Supports operating temperature from -25°C to +70°C

Excellent resistance to mechanical shock and vibration



Conforming to CE, CCC and ROHS standards

Up to IP65 protection ratings