

# Product data sheet

Specifications



## Push button, Type B, standard duty control station, 5A, 600 VAC, UP/DOWN, NEMA 7/9

9001BR208

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Main

Range of Product	Harmony 9001B
Product or Component Type	Complete control station
Device short name	9001BR
Control station application	Two functions
Colour of base of enclosure	Grey

### Complementary

Material	Cast zinc
Marking	CE
Type of operator	momentary
Control station composition	1 push-button, black, white FOR 1 push-button, black, white REV
Contacts type and composition	1 NO + 1 NO
Mechanical durability	5000000 cycles
[Ie] rated operational current	5 A 600 V, AC
Device mounting	Surface
Type of Installation	Indoor

### Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
NEMA degree of protection	NEMA 7/9
Product Certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Environmental characteristic	Hazardous location

### Ordering and shipping details

Category	US10CS121421
Discount Schedule	0CS1
GTIN	785901856542
Returnability	No
Country of origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

---

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	13.97 in (35.484 cm)
Package 1 Width	5.50 in (13.97 cm)
Package 1 Length	35.48 in (90.129 cm)
Package weight(Lbs)	3.580 lb(US) (1.624 kg)

## Contractual warranty

---

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	<b>WARNING:</b> This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>

## Use Again

### Repack and remanufacture

Take-back	No
-----------	----

## Technical Illustration

## Dimensions

