

Product data sheet

Specifications



Switch, X Series, 15A, single pole, 1 way, white, 30 pcs

SQR14103WH

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Square D X Series
Product or Component Type	Switch
Device Application	Control
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series

Complementary

Actuator	Dolly
Number of modules	1
Colour tint	white
Number of gangs	1 gang
Number of poles	1
Switch Function	1-way
[Ie] rated operational current AC	15 A
[Ue] rated operational voltage	120 V 277 V
Network type	AC
Network Frequency	60 Hz
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic: strap Metal: fixing frame
Color	White
Surface Finish	Matte
Connections - terminals	Phase and neutral 2 screw terminal AWG 14...AWG 12) copper Phase and neutral 2 push-in termination AWG 14), solid copper Earth 1 screw terminal copper
Earth circuit	Self earthing
Width	1.5 in (37 mm)
Height	4.06 in (103 mm)
Depth	1.4 in (35 mm)
Quantity per Set	30 pieces
Market Segment	Residential

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Targeted channel	Distributor
------------------	-------------

Environment

Standards	UL 20
Product Certifications	cULus

Ordering and shipping details

Category	US10DE909932
Discount Schedule	ODE9
GTIN	785901534570
Returnability	Yes
Country of origin	VN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.50 in (3.8 cm)
Package 1 Width	1.46 in (3.7 cm)
Package 1 Length	4.11 in (10.44 cm)
Package weight(Lbs)	2.05 oz (58.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	30
Package 2 Height	4.84 in (12.3 cm)
Package 2 Width	4.17 in (10.6 cm)
Package 2 Length	14.88 in (37.8 cm)
Package 2 Weight	4.101 lb(US) (1.860 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	180
Package 3 Height	10.43 in (26.5 cm)
Package 3 Width	13.11 in (33.3 cm)
Package 3 Length	15.67 in (39.8 cm)
Package 3 Weight	26.2 lb(US) (11.9 kg)

Contractual warranty

Warranty	2 years
----------	---------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

Circularity Profile No need of specific recycling operations

Take-back No

Technical Illustration

Wiring diagram




Image of product / Alternate images

Alternative

