

# Product data sheet

Specifications



Disconnect switch, TeSys VLS, protruding rotary handle, hole mounting, 65x65mm, red handle, 5mm shaft, defeatable

VLSH2H5RD

Product availability: Stock - Normally stocked in distribution facility

## Main

|                           |                                         |
|---------------------------|-----------------------------------------|
| Range                     | TeSys                                   |
| Device short name         | VLSH                                    |
| Product or Component Type | Rotary handle                           |
| Range compatibility       | TeSys TeSys VARIO LS VLS3P              |
| Handle colour             | Red                                     |
| Handle front plate colour | Yellow                                  |
| Rotary handle padlocking  | 1 to 3 padlocks 0.2...0.3 in (4...8 mm) |
| Marking                   | 0 - 1                                   |

## Complementary

|                   |                         |
|-------------------|-------------------------|
| Fixing mode       | Hole 0.9 in (22.5 mm)   |
| Tightening torque | 20.4 lbf.in (2.3 N.m)   |
| Base dimension    | 65 x 65 mm              |
| Height            | 2.6 in (65 mm)          |
| Width             | 2.6 in (65 mm)          |
| Depth             | 2.9 in (72.5 mm)        |
| Product Weight    | 0.141 lb(US) (0.064 kg) |

## Environment

|                           |                                                                                                                   |
|---------------------------|-------------------------------------------------------------------------------------------------------------------|
| IP Degree of Protection   | IP65                                                                                                              |
| NEMA degree of protection | NEMA 1<br>NEMA 2 UL 508<br>NEMA 3R UL 508<br>NEMA 4 UL 508<br>NEMA 4X UL 508<br>NEMA 12 UL 508<br>NEMA 12K UL 508 |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US10CP121734  |
| Discount Schedule | 0CP1          |
| GTIN              | 3606481156921 |
| Returnability     | Yes           |
| Country of origin | IT            |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Nbr. of units in pkg.        | 1                       |
| Package 1 Height             | 1.97 in (5.000 cm)      |
| Package 1 Width              | 2.56 in (6.500 cm)      |
| Package 1 Length             | 2.56 in (6.500 cm)      |
| Package weight(Lbs)          | 2.187 oz (62.000 g)     |
| Unit Type of Package 2       | S02                     |
| Number of Units in Package 2 | 40                      |
| Package 2 Height             | 5.91 in (15.000 cm)     |
| Package 2 Width              | 11.81 in (30.000 cm)    |
| Package 2 Length             | 15.75 in (40.000 cm)    |
| Package 2 Weight             | 6.184 lb(US) (2.805 kg) |

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

|  Materials and Substances |                                                            |
|------------------------------------------------------------------------------------------------------------|------------------------------------------------------------|
| Packaging made with recycled cardboard                                                                     | Yes                                                        |
| Packaging without single use plastic                                                                       | No                                                         |
| <a href="#">EU RoHS Directive</a>                                                                          | Pro-active compliance (Product out of EU RoHS legal scope) |

Use Again

|  Repack and remanufacture |    |
|------------------------------------------------------------------------------------------------------------|----|
| Take-back                                                                                                  | No |