

Product data sheet

Specifications



Fixing plate for use on vertical support for modular tower lights, Harmony XVU, black, 60mm

XVUZ12

⚠ To be discontinued on: May 31, 2026

⚠ To be discontinued

Main

Range of product	Harmony XVU
Product or component type	Modular tower light
Accessory / separate part type	Fixing plate
Accessory / separate part category	Mounting and fixing accessory
Component name	XVU
Mounting diameter	60 mm

Complementary

Mounting support	Wall mounted
Product compatibility	XVUZ05 XVUZ800 XVUZ400 XVUZ02Q XVUZ02
Material	Aluminium V-0 conforming to UL 94
Housing colour	Black
[Us] rated supply voltage	24 V AC/DC 110...240 V AC
Length	8 mm
Product weight	0.36 kg

Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...50 °C
IP degree of protection	IP65
Product certifications	CSA UL CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	7.000 cm

Package 1 Length	11.500 cm
Package 1 Weight	496.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.193 kg
Unit Type of Package 3	P06
Number of Units in Package 3	320
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	176.176 kg



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 3

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number C06fce4f-aea2-46a5-aadb-0b38d1efbe3f

California proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture


End of life manual availability [End of Life Information](#)

Take-back No


Dimensions Drawings

Dimensions


Rear View



Side View




Mounting and Clearance

Vertical Support Panel Drillings

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

功能特点

Harmony XVU 模块式信号灯柱



单色 LED 发光单元 6 色可选;
多色 LED 发光单元: 旋钮手调或者 PLC 信号控制, 可发出多种颜色光, 多种闪烁模式

模块化结构 客户自行组装。
可组合最多 5 个发光单元
或 4 个发光 +1 个发声单元

水平安装: 使用直接安装底座,
支撑杆安装底座或可伸缩支撑
杆安装底座固定到安装面板上;
竖直安装: 使用带 L 支架支撑杆
安装底座或添加墙装支架固定
到竖直安装面板上

安装简化, 维护方便,
可直接连接 PLC

使用免费的语音编辑软件在电脑上定
制语音, 再通过 SD 卡复制到设备中,
多个通道可输出。

Image of product / Alternate images

Alternative







Image of product in real life situation

