

Product data sheet

Specifications



Wall mounted enclosure, PanelSeT S3X, stainless steel 304L, double plain door, 1200x1000x300mm, IP55

NSYS3X121030

Main

Range	Spacial
Product name	Spacial S3X
enclosure type	Multi-purpose
category	Compact enclosure
nominal height	1200 mm
nominal width	1000 mm
nominal depth	300 mm
product installation	Wall-mounting
Device composition	1 body 2 door 1 lock: door 1 reinforcement frame drilled: door

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 2 door(s)
Door opening side	Reversible (120 °)
Lock type	3 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door: stainless steel 304L Hinge: stainless steel
Surface finish	Body and door: Scotch-Brite® brushed
Product weight	51.8 kg

Environment

Standards	IEC 62208 UL CUL
Product certifications	CAN/CSA 22 UL 508 type A

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Specific hygiene Corrosive

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	32.000 cm
Package 1 Width	101.000 cm
Package 1 Length	122.000 cm
Package 1 Weight	51.800 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	3
Package 2 Height	117.000 cm
Package 2 Width	100.000 cm
Package 2 Length	122.000 cm
Package 2 Weight	179.400 kg

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	770
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No

Offer Marketing Illustration

Product benefits / Features

