

Product data sheet

Specifications



Padlockable guard for mushroom head 40mm, Harmony XB4, metal, red

ZBZ1604

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XB5 Harmony XB4
Product or Component Type	Guard
Accessory / separate part category	Isolation accessory
Product Compatibility	XB5AS... XB5AT... XB4BS... XB4BT...
Accessory / separate part destination	Ø 40 mm emergency stop push-button For standard head
Color	Red
Quantity per Set	Set of 1

Complementary

Material	Metal
Product Weight	0.101 lb(US) (0.046 kg)

Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
GTIN	3389110099485
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.20 in (5.600 cm)
Package 1 Width	1.97 in (5.000 cm)
Package 1 Length	1.77 in (4.500 cm)
Package weight(Lbs)	2.046 oz (58.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	160
Package 2 Height	11.81 in (30.000 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	21.566 lb(US) (9.782 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

1

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

Take-back	No
-----------	----

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XB4

Conformity with IEC, UL, CSA, CCC EAC, and JIS standards, as well as CE marking and marine approvals

Up to IP66, 67, 69, 69K, and type 4X protection ratings

High vibration resistance with shake-proof terminal screws

Operating temperature from -40°C to 70°C

Shock protection level up to IK06

Secure switching of inductive or heavy DC loads directly – 100 000 operations at 10A, 24V dc

Offer Marketing Illustration

Product benefits / Features




Image of product / Alternate images

Alternative





