

# Product data sheet

## Characteristics

### ZC2GG1

auxiliary contact block - 1 NO + 1 NC - On delay - for TeSys B



#### Main

Range of product	TeSys B
Range	TeSys
Product or component type	Auxiliary contact block
Product compatibility	CR1B LC1B
Pole contact composition	1 NO + 1 NC

#### Complementary

Mechanical durability	1000000 cycles
Connections - terminals	Control circuit screw connection 1 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) with cable end Control circuit screw connection 1 0.01 in <sup>2</sup> (6 mm <sup>2</sup> ) without cable end Control circuit screw connection 2 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) with cable end Control circuit screw connection 2 0.01 in <sup>2</sup> (6 mm <sup>2</sup> ) without cable end

#### Ordering and shipping details

Category	18073 - SPARE PARTS DISCOUNT I
Discount Schedule	CP2
GTIN	03389110365481
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	FR

#### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.76 in (7 cm)
Package 1 width	4.17 in (10.6 cm)
Package 1 Length	4.21 in (10.7 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	25
Package 2 Weight	29.05 lb(US) (13.177 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------