

Product data sheet

Characteristics

XBTZ9018

RS485 cable for Schneider Electric PLC Twido/
Micro/Premium, HMI Sub-D9 to PLC Mini-Din8



Main

Range of Product	Harmony XBT
Accessory / separate part category	Connection accessories
Product or Component Type	Connecting cable
Accessory / Separate Part Type	Connecting cable
Accessory / separate part designation	Uni-Telway/Modbus serial link
Accessory / separate part destination	XBT terminal
Cable length	8.20 ft (2.5 m)

Complementary

Product Compatibility	XBTGT2... XBTGK....
Range Compatibility	Twido Modicon Premium automation platform Modicon TSX Micro Harmony HMI GTO
Electrical connection	1 female connector mini DIN, 8 pins
Communication port protocol	Modbus Uni-Telway
Physical interface	RS485
Net Weight	0.37 lb(US) (0.17 kg)

Ordering and shipping details

Category	22570-MAGELIS TEXT DISPLAYS & ACCESS
Discount Schedule	MC2
GTIN	3595864012995
Nbr. of units in pkg.	1
Package weight(Lbs)	4.20 oz (119.0 g)
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.59 in (1.5 cm)
Package 1 width	5.91 in (15.0 cm)
Package 1 Length	6.50 in (16.5 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------