

Product data sheet

Specifications



Multisound siren, Harmony XVS,
prewired, white colour, 0...105dB,
43tones, 240V AC

XVS14MMW

Main

Range of product	Harmony XVS
Product or component type	Multisound siren
Device short name	XVS

Complementary

Colour	White
Material	PC (polycarbonate): back cover PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): front PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): back
Product weight	1.2 kg
Marking	CE
Mounting support	Bracket
fixing mode	3 holes Ø 9 mm
[Uiimp] rated impulse withstand voltage	4 kV
Current consumption	50 mA at 240 V
Electrical connection	Cable: 6.5...8.5 mm, 0.33 mm ² / AWG 22 (signalling circuit) Cable: 6.5...8.5 mm, 0.52 mm ² / AWG 20 (power circuit)
Width	140 mm
Height	114 mm
Depth	223 mm

Environment

Signalling type	43 tones siren
Standards	IEC 61000-6-3 IEC 60947-5-1 EN 60947-01 IEC 61000-6-2
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP53 conforming to IEC 60529
[Us] rated supply voltage	240 V AC

Noise level	0...105 dB (continuous or intermittent tone) at 1 m
-------------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	15.5 cm
Package 1 Length	27.5 cm
Package 1 Weight	1.55 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	10.676 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint **12**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

California proposition 65 **WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

Use Again

Repack and remanufacture


End of life manual availability [End of Life Information](#)

Take-back **No**

Dimensions Drawings

Siren

Dimensions



Technical Illustration

Dimensions




Image of product / Alternate images

Alternative

