

# Product data sheet

## Characteristics

# 9001SKR24RH6

Push-button, Harmony 9001SK, plastic, mushroom 35mm, red, 30mm, spring return, 1 NC



### Main

|                                 |                                 |
|---------------------------------|---------------------------------|
| Range of Product                | Harmony 9001SK                  |
| Product or Component Type       | Push-button                     |
| Device short name               | 9001SK                          |
| Type of operator                | Spring return                   |
| Operator profile                | Red mushroom Ø 35 mm            |
| Operator additional information | Screw-on plastic with set screw |

### Complementary

|                               |                  |
|-------------------------------|------------------|
| Bezel material                | Plastic          |
| Mounting diameter             | 1.18 in (30 mm)  |
| Contacts type and composition | 1 NC             |
| Contact operation             | Standard         |
| Mechanical durability         | 5000000 cycles   |
| Device presentation           | Complete product |
| Cap/operator or lens colour   | Red              |
| Operator profile              | Mushroom Ø 35 mm |
| Type of operator              | Spring return    |
| Size                          | 30 mm            |

### Environment

|                           |  |
|---------------------------|--|
| Standards                 | EN/IEC 60947-5-1<br>CSA C22.2 No 14<br>JIS C 852<br>JIS C 4520<br>UL 508<br>EN/IEC 60947-5-4<br>EN/IEC 60947-1 |
| IP degree of protection   | IP66   |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13   |

### Ordering and shipping details

|                   |                   |
|-------------------|-------------------|
| Category          | 21429-9001 SK,SKY |
| Discount Schedule | CS1               |
| GTIN              | 785901039723      |
| Returnability     | No                |
| Country of origin | MX                |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 5.08 in (12.903 cm)  |
| Package 1 Width              | 2.00 in (5.08 cm)    |
| Package 1 Length             | 12.90 in (32.774 cm) |
| Package 1 Weight             | 8.00 oz (226.796 g)  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           |  <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information |  <a href="#">Yes</a>   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|