

Product data sheet

Characteristics

9001KR9P38LRRH2

PUSH BUTTON 600VAC 10A 30MM T-K



Main

| | |
|---------------------------------|-----------------------|
| Range of product | Harmony 9001K |
| Product or component type | Push-button |
| Device short name | K |
| Operator additional information | Full guard in plastic |

Complementary

| | |
|--------------------------------|----------------------------|
| Bezel material | Chromium plated metal |
| Mounting diameter | 1.18 in (30 mm) |
| Light source | Without |
| Light block supply | Without supply |
| Contacts type and composition | 2 NO + 2 NC |
| [Ie] rated operational current | 10 A, AC-15 10 A, DC-13 |
| Contact operation | Standard |
| Device presentation | Complete product |

Environment

| | |
|---------------------------|--|
| Product certifications | CSA LR 25490 class 3211 03 CE UL listed file E42259 CCN NKCR NEMA |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| | |
|---------------------|-----------------------------|
| Category | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| GTIN | 00785901527176 |
| Package weight(Lbs) | 8.00 oz (226.796 g) |
| Returnability | No |
| Country of origin | MX |

Offer Sustainability

| | |
|---------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|----------------------------|--|
| RoHS exemption information | <input checked="" type="checkbox"/> Yes |
| China RoHS Regulation | <input checked="" type="checkbox"/> China RoHS Declaration |
| Environmental Disclosure | <input checked="" type="checkbox"/> Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|
