

# Product data sheet

Specifications



## KIT FLUSH-MOUNTING POUR ATV T2

NSYPTDS2

**Product availability: Stock - Normally stocked in distribution facility**

### Main

Range	PanelSeT
Product or Component Type	Drive flush mounting kit
accessory category	Mounting and fixing accessory
Product Specific Application	Process and utilities
Range compatibility	Altivar variable speed drive ATV630 Altivar variable speed drive ATV930 PanelSeT SF and SM enclosures 19.7 in (500 mm) x 11.8 in (300 mm) PanelSeT S3D enclosure 19.7 in (500 mm) x 11.8 in (300 mm)
compatibility for Altivar Process 630-930, size:	2
Motor power kW	5.5 kW 220/240 V 7.5 kW 380/480 V 11 kW
Mounting location	1 back of enclosure mounting plate 2 inside enclosure
Kit composition	1 x mounting plate with flanges and integrated gasket, steel with anti-corrosive coating by screws and nuts 1 x fixing accessories 1 x drilling template 1 x instruction sheet 1 x edge protector profile, plastic

### Complementary

Permanent permissible load	17.0 lb(US) (7.7 kg)
color	Gray RAL 7035)
Height	External: 16.5 in (420 mm) Cut-out: 14.8 in (375 mm)
Width	External: 10.4 in (265 mm) Cut-out: 8.5 in (215 mm)
Depth	Wall-enclosure separation : 0.9 in (22 mm)
Product Weight	4.237 lb(US) (1.922 kg)
Services	Configuration of enclosure pre-drilled back Factory installation drive flush mounting kit

### Environment

IP degree of protection IP55 conforming to IEC 60529

### Ordering and shipping details

Category	US1CP4E22276
Discount Schedule	CP4E

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	3606485433219
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	11.42 in (29.000 cm)
Package 1 Length	17.32 in (44.000 cm)
Package weight(Lbs)	4.237 lb(US) (1.922 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	30
Package 2 Height	19.69 in (50.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	160.938 lb(US) (73.000 kg)

## Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACH Regulation	<a href="#">REACH Declaration</a>

## Use Again

### Repack and remanufacture

Take-back	No
-----------	----