

Product data sheet

Specifications



Neon/incandescent bulb, Harmony XB2, multi-button control station, for 22mm push button, front mounting, bulb not included

ZB2BV006

Product availability: Stock - Normally stocked in distribution facility

Complementary

Bulb type	Neon Incandescent
Control station category	Multi-button
Enclosure Material	Polypropylene
Light block supply	Direct
Light source	Bulb not included
Mounting of block	Front mounted
Net Weight	0.033 lb(US) (0.015 kg)
Supply	Direct
[Us] rated supply voltage	<= 400 V

Ordering and shipping details

Category	US10CS222461
Discount Schedule	0CS2
GTIN	3389110645385
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.26 in (3.2 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	1.77 in (4.5 cm)
Package weight(Lbs)	0.8 oz (22.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	100
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	5.617 lb(US) (2.548 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Easy Harmony XB2

Supports operating temperature from -25°C to +70°C

Excellent resistance to mechanical shock and vibration



Conforming to CE, CCC and ROHS standards

Up to IP65 protection ratings

Offer Marketing Illustration

Product benefits / Features

Features

Easy Harmony XB2



Metal bezels with metal fixing collars for impact endurance

Designed to be used in numerous control and signaling applications

Metal screws for secure fix, grounding contact to the panel and anti-rotation

Simple modular design facilitates post installation servicing, modification and adaption of machines by non-specialists

Available in sub-assemblies for easy mix and match of functionalities