

# Product data sheet

## Characteristics

### XBTZ9732

direct connection cable - L = 2.5 m - 1 Micro-logix 1000 - DH485



#### Main

Range of Product	Harmony XBT
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / separate part designation	Direct connection cable
Accessory / separate part destination	XBT terminal
Cable length	8.20 ft (2.5 m)

#### Complementary

Product Compatibility	XBTR411 XBTN410 XBTNU400 XBTN401 XBTR410
Range Compatibility	Allen-Bradley SLC5
Electrical connection	1 connector Micro-logix 1000
Communication Port Protocol	DH485
Physical interface	RS232
Net Weight	0.46 lb(US) (0.21 kg)

#### Ordering and shipping details

Category	22570-MAGELIS TEXT DISPLAYS & ACCESS
Discount Schedule	MC2
GTIN	3389110179514
Returnability	No
Country of origin	FR

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	1.18 in (3.0 cm)
Package 1 Length	5.91 in (15.0 cm)
Package 1 Weight	6.77 oz (192.0 g)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------