

Product data sheet

Specifications



Selector switch head, Harmony 9001SK, plastic, standard handle, black, 30mm, 3 positions, Cam F, stay put

9001SKS46B

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type	Head for selector switch
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Range of Product	Harmony 9001SK

Complementary

Bezel material	Plastic
Cap/operator or lens colour	black
Contacts type and composition	Without contact block
Operator position information	3 positions
Operator profile	Standard handle
Operator profile	1 projecting push-button
Size	30 mm
Type of operator	Maintained
Cap/operator or lens colour	Black
Type of operator	Stay put
Contacts type and composition	Without contact block

Environment

NEMA Degree of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
GTIN	785901959861
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nbr. of units in pkg.	1
Package 1 Height	2.00 in (5.080 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	2.80 in (7.112 cm)
Package weight(Lbs)	2.081 oz (59.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	15
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	2.392 lb(US) (1.085 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	480
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	94.182 lb(US) (42.720 kg)

Contractual warranty

Warranty	18 months
-----------------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile No need of specific recycling operations

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001SK



Image of product / Alternate images

Alternative





