

Product data sheet

Specifications



Cable end, Linergy TR cable ends, twin conductor, blue, 2.5mm², for insulated cable, medium size, 5 sets of 50

AZ5DE025D

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Linergy
Product or Component Type	Cable end
Cable end size	Medium
Standards	DIN 46228-4
Type of Packing	Dispenser pack
Quantity per Set	5 sets of 50
Cable cross section	0.004 in ² (2.5 mm ²)

Complementary

Cable end type	Twin conductor
Additional information	Without marker tag holder
Color	Gray
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	2
AWG Gauge	AWG 14
Bezel size	Ø 4.2 x 7.8 mm
Tube diameter	0.1 in (3.2 mm)
Length	0.7 in (18.5 mm)
Tube length	0.4 in (10 mm)
Product Weight	0.320 lb(US) (0.145 kg)

Environment

Product Certifications	cCSAus
Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
GTIN	3389110518924
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin	DE
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	0.16 in (0.400 cm)
------------------	--------------------

Package 1 Width	0.16 in (0.400 cm)
-----------------	--------------------

Package 1 Length	0.55 in (1.400 cm)
------------------	--------------------

Package weight(Lbs)	0.011 oz (0.300 g)
---------------------	--------------------

Unit Type of Package 2	BB1
------------------------	-----

Number of Units in Package 2	250
------------------------------	-----

Package 2 Height	5.12 in (13.000 cm)
------------------	---------------------

Package 2 Width	2.76 in (7.000 cm)
-----------------	--------------------

Package 2 Length	4.96 in (12.600 cm)
------------------	---------------------

Package 2 Weight	4.762 oz (135.000 g)
------------------	----------------------

Unit Type of Package 3	S02
------------------------	-----

Number of Units in Package 3	2500
------------------------------	------

Package 3 Height	5.91 in (15.000 cm)
------------------	---------------------

Package 3 Width	11.81 in (30.000 cm)
-----------------	----------------------

Package 3 Length	15.75 in (40.000 cm)
------------------	----------------------

Package 3 Weight	3.726 lb(US) (1.690 kg)
------------------	-------------------------

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No