

Product data sheet

Specifications



APC Symmetra LX Battery Module



SYBT5

Overview

| | |
|--------------|---|
| Presentation | Extended run power protection for servers, networks, and telecommunications |
| Lead time | Usually in Stock |

Main

| | |
|---------------------------|--------------------------|
| Product or Component Type | Battery accessory |
| Number of rack unit | 0U |
| Number of cables | 1.0 |
| Battery Type | Lead-Acid battery |
| Provided Equipment | Installation guide |
| Range of Product | Symmetra Battery Systems |

Batteries & Runtime

| | |
|---------------------------|----------------------------|
| Battery location | Internal Battery |
| Battery blocks per string | 10 |
| Battery Slots Empty | 0 |
| Included Battery Modules | 0 |
| Device mounting | Enclosed battery cartridge |
| Battery Voltage | 120 V |
| RBC Quantity | 1 |

Physical

| | |
|----------------|-----------------------|
| Height | 5.51 in (14 cm) |
| Width | 8.27 in (21 cm) |
| Depth | 21.50 in (54.6 cm) |
| Net Weight | 64.2 lb(US) (29.1 kg) |
| Mounting Mode | Not rack-mountable |
| USB compatible | No |

Conformance

| | |
|------------------------|---------|
| Standards | UL 1778 |
| Product Certifications | CSA |

Environmental

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|---------------------------------------|---------------------------|
| Ambient air temperature for operation | 32...104 °F (0...40 °C) |
| Operating altitude | 0...10000 ft |
| Relative Humidity | 0...95 % |
| Ambient Air Temperature for Storage | 5...113 °F (-15...45 °C) |
| Storage altitude | 0...15000 ft (0...4572 m) |
| Storage Relative Humidity | 0...95 % |

Ordering and shipping details

| | |
|-------------------|-----------------------------|
| Category | 11309 - APC RESALE PRODUCTS |
| GTIN | 731304218869 |
| Returnability | No |
| Country of origin | PH |

Packing Units

| | |
|------------------------------|-----------------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 10.63 in (27.000 cm) |
| Package 1 Width | 11.42 in (29.000 cm) |
| Package 1 Length | 29.92 in (76.000 cm) |
| Package weight(Lbs) | 67.241 lb(US) (30.500 kg) |
| Unit Type of Package 2 | P12 |
| Number of Units in Package 2 | 8 |
| Package 2 Height | 29.53 in (75.000 cm) |
| Package 2 Width | 31.50 in (80.000 cm) |
| Package 2 Length | 47.24 in (120.000 cm) |
| Package 2 Weight | 564.384 lb(US) (256.000 kg) |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

1

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

Take-back

Yes

WEEE Label

 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



