

Product data sheet

Specifications



Socket, SE Relays general purpose relay accessory, 3PDT, 15A, 300 V, 11 pins, pins for printed circuit board, 788 S

70-178-2

Product availability: Stock - Normally stocked in distribution facility

Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	relay 788XBXR/XCXR
Number of Terminals	11
Switch Function	3PDT
Contact Composition	3 NO + 3 NC

Complementary

Rated Current	15 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Pin pins for printed circuit board, clamping connection capacity:1 mm ² , AWG 16 solid for output Panel pins for printed circuit board, clamping connection capacity:1 mm ² , AWG 16 stranded for output
Fixing Mode	By screws printed circuit boards
Product Weight	0.4 oz (12.1 g)
Width	1.5 in (38.1 mm)
Depth	1.4 in (34.8 mm)

Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

Ordering and shipping details

Category	US10CP221127
Discount Schedule	OCP2
GTIN	3606480277801

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
---------------	-----

Country of origin	CN
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	1.37 in (3.47 cm)
------------------	-------------------

Package 1 Width	1.50 in (3.81 cm)
-----------------	-------------------

Package 1 Length	0.47 in (1.201 cm)
------------------	--------------------

Package weight(Lbs)	0.4 oz (12.1 g)
---------------------	-----------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard No

Packaging without single use plastic No

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation [REACH Declaration](#)

California proposition 65 WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile No need of specific recycling operations

Take-back No

Dimensions Drawings

Approximate Dimensions

