

Product data sheet

Specifications



Occupancy and humidity sensor, X Series, PIR, single pole, 1 way, black, matte finish

SQR73105BK

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Square D X Series
Product or Component Type	Sensor
Device Application	Control
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series
Number of gangs	1 gang
Number of poles	1

Complementary

Switch Function	1-way
Sensor Type	PIR Humidity sensor Light level sensor
[Ie] rated operational current AC	10 A
[Ue] rated operational voltage	120 V
Network type	AC
Network Frequency	60 Hz
Load type	Halogen 0...500 W Incandescent 0...500 W Dimmable LED 0...150 W Fan motor 2.5 A
Maximum Horse Power Rating	0.25 hp
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic: strap Metal: fixing frame
Color	Black
surface treatment	Painted
Surface Finish	Matte
Marking	LIGHT-FAN
Width	1.7 in (43 mm)
Height	4.06 in (103 mm)
Quantity per Set	1 piece

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cULus ICES-003
Standards	UL 1917

Ordering and shipping details

Category	US10DE909933
Discount Schedule	ODE9
GTIN	785901549253
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	4.17 in (10.6 cm)
Package 1 Width	2.44 in (6.2 cm)
Package 1 Length	2.56 in (6.5 cm)
Package weight(Lbs)	7.05 oz (200 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.45 in (11.3 cm)
Package 2 Width	5.39 in (13.7 cm)
Package 2 Length	12.60 in (32.0 cm)
Package 2 Weight	4.103 lb(US) (1.861 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	40
Package 3 Height	13.39 in (34.0 cm)
Package 3 Width	9.45 in (24.0 cm)
Package 3 Length	11.65 in (29.6 cm)
Package 3 Weight	17.730 lb(US) (8.042 kg)

Contractual warranty

Warranty	2 year
----------	--------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

California proposition 65 WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back No

Technical Illustration

Wiring diagram




Image of product / Alternate images

Alternative

