

# Product data sheet

Specifications



Disconnect switch, TeSys VLS, coupling system for 6 to 8 pole switch disconnectors, size 1, 16A to 40A devices

VLS8M1

**Product availability:** Stock - Normally stocked in distribution facility

## Main

Range	TeSys
Product or Component Type	Mechanical interlock
Accessory / separate part category	Coupling accessory
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Black
Handle front plate colour	Grey
Rotary handle padlocking	1 padlock 0.2 in (4 mm)
Marking	0 - 1

## Complementary

Fixing Mode	By clips and screws
Tightening torque	4.4 lbf.in (0.5 N.m)
Height	1.8 in (45 mm)
Width	2.8 in (72 mm)
Depth	1.06 in (27 mm)
Net Weight	0.11 lb(US) (0.05 kg)

## Environment

Standards	UL 508 CSA C22.2 No 14
Product Certifications	cULus EAC
IP Degree of Protection	IP20

## Ordering and shipping details

Category	US10CP121734
Discount Schedule	0CP1
GTIN	3606481156877
Returnability	Yes
Country of origin	IT

## Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Unit Type of Package 1</b>	PCE
<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	1.85 in (4.700 cm)
<b>Package 1 Width</b>	2.56 in (6.500 cm)
<b>Package 1 Length</b>	3.54 in (9.000 cm)
<b>Package weight(Lbs)</b>	2.434 oz (69.000 g)
<b>Unit Type of Package 2</b>	S02
<b>Number of Units in Package 2</b>	28
<b>Package 2 Height</b>	5.91 in (15.000 cm)
<b>Package 2 Width</b>	11.81 in (30.000 cm)
<b>Package 2 Length</b>	15.75 in (40.000 cm)
<b>Package 2 Weight</b>	4.903 lb(US) (2.224 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)

## Use Again

### Repack and remanufacture

Take-back	No
-----------	----