

# Product data sheet

Specifications



Wall mounted enclosure, PanelSeT  
S3X, stainless steel 304L, plain  
door, 1000x800x300mm, IP66

NSYS3X10830

## Main

Range	Spacial
Product name	Spacial S3X
enclosure type	Multi-purpose
category	Compact enclosure
nominal height	1000 mm
nominal width	800 mm
nominal depth	300 mm
product installation	Wall-mounting
Device composition	1 body 1 reinforcement frame drilled: door 1 door 2 lock: door

## Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net weight	37.4 kg

## Environment

Standards	IEC 62208 UL CUL
-----------	------------------------

<b>Product certifications</b>	UL 508 type A CAN/CSA 22
<b>IP degree of protection</b>	IP66 conforming to IEC 60529
<b>IK degree of protection</b>	IK10 conforming to IEC 62262
<b>Environmental characteristic</b>	Corrosive Specific hygiene

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	32.000 cm
<b>Package 1 Width</b>	82.000 cm
<b>Package 1 Length</b>	103.000 cm
<b>Package 1 Weight</b>	37.400 kg
<b>Unit Type of Package 2</b>	PAM
<b>Number of Units in Package 2</b>	6
<b>Package 2 Height</b>	178.000 cm
<b>Package 2 Width</b>	100.000 cm
<b>Package 2 Length</b>	120.000 cm
<b>Package 2 Weight</b>	236.000 kg

## Contractual warranty

<b>Coverage</b>	Core product
<b>Warranty</b>	18 months



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	556
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	<a href="#">REACh Declaration</a>

### Use Again

#### Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No

## Offer Marketing Illustration

### Product benefits / Features

---

