

Product data sheet

Specifications



Legend holder 60mm for emergency stop, plastic, Harmony XB4, yellow, for padlocking, marked EMERGENCY STOP

ZBY9330T

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XB5 Harmony XB4
Product or Component Type	Marked legend
Accessory / Separate Part Type	Legend
Accessory / separate part category	Marking accessories
Accessory / separate part destination	Emergency stop mushroom head push-button for ZBZ3605 and padlocking kit
Marking	Black EMERGENCY STOP yellow
Label dimensions	Ø 60 mm
User Language	English

Complementary

Sale per indivisible quantity	10
Material	Plastic
Product Weight	0.009 lb(US) (0.004 kg)
Main group	E-stop

Environment

Standards	EN/ISO 13850: 2006 IEC 60204-1
-----------	-----------------------------------

Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
GTIN	3389119020510
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.04 in (0.100 cm)
Package 1 Width	2.56 in (6.500 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	2.56 in (6.500 cm)
Package weight(Lbs)	0.032 oz (0.900 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	0.04 in (0.100 cm)
Package 2 Width	2.60 in (6.600 cm)
Package 2 Length	2.76 in (7.000 cm)
Package 2 Weight	0.705 oz (20.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	250
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	25.079 oz (711.000 g)

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

1

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back

No

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XB4

Conformity with IEC, UL, CSA, CCC EAC, and JIS standards, as well as CE marking and marine approvals

Up to IP66, 67, 69, 69K, and type 4X protection ratings

High vibration resistance with shake-proof terminal screws

Operating temperature from -40°C to 70°C

Shock protection level up to IK06

Secure switching of inductive or heavy DC loads directly – 100 000 operations at 10A, 24V dc

Offer Marketing Illustration

Product benefits / Features




Image of product / Alternate images

Alternative





