

Product data sheet

Specifications



Prewired rotating mirror beacon,
Harmony XVR, 120mm, blue,
without buzzer, 24V AC/DC

XVR12B06

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XVR
Product or Component Type	Prewired rotating mirror beacon
Sound signalling	Without
Device short name	XVR
Mounting diameter	4.7 in (120 mm)
IP degree of protection	IP23 IEC 60529
[Us] rated supply voltage	24 V AC/DC
Light source	High luminosity LED, blue

Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part AS: globe
CAD overall width	4.7 in (120 mm)
CAD overall depth	4.7 in (120 mm)
Net Weight	1.1 lb(US) (0.5 kg)
Marking	CE
Product mounting	By 3 M5 screws
Supply voltage limits	19...30 V DC 21.6...26.4 V AC
[Uiimp] rated impulse withstand voltage	0.8 kV
Current Consumption	125 mA
Flashing frequency	2.3 Hz
Clamping Connection Capacity	0.83 mm ²
AWG Gauge	AWG 18
Cable length	15.7 in (400 mm)

Environment

Standards	IEC 61000-6-2 IEC 61000-6-4
Protective treatment	TC
Ambient Air Temperature for Storage	-31...158 °F (-35...70 °C)
Ambient Air Temperature for Operation	14...122 °F (-10...50 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US100XV22617
Discount Schedule	00XV
GTIN	3606480033186
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	5.51 in (14 cm)
Package 1 Width	5.59 in (14.2 cm)
Package 1 Length	7.68 in (19.5 cm)
Package weight(Lbs)	22.4 oz (634 g)
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	14.279 lb(US) (6.477 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **13**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

California proposition 65 **WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

Use Again

Repack and remanufacture


Circularity Profile [End of Life Information](#)

Take-back **No**

Dimensions Drawings

Rotating Mirror Beacon


Dimensions



Mounting and Clearance

Rotating Mirror Beacon

Panel Cut-out



Technical Illustration

Dimensions

