

Product data sheet

Specifications



30mm Push Buttons, package containing 9001KR1UH13
momentary push button operator,
START and STOP legend plates

9001AB1

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------------------------|---|
| Range of Product | Harmony 9001K |
| Product or Component Type | Push-button |
| Device short name | K |
| Type of operator | spring return |
| Operator profile | White full guard Orange full guard Black full guard Red full guard Green full guard Yellow full guard Blue full guard |
| Operator additional information | With 2 legends START and STOP |

Complementary

| | |
|--------------------------------|----------------------------|
| Bezel material | Chromium plated metal |
| Mounting diameter | 1.2 in (30 mm) |
| Contacts type and composition | 1 C/O |
| [Ie] rated operational current | 10 A, AC-15 10 A, DC-15 |
| Contact operation | Standard |
| Device presentation | Complete product |
| Cap/operator or lens colour | 7 colours choice |

Environment

| | |
|---------------------------|--|
| Product Certifications | CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR CE NEMA |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US1IPOP22750 |
| Discount Schedule | IPOP |
| GTIN | 785901849179 |
| Returnability | Yes |
| Country of origin | MX |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 5.10 in (12.954 cm) |
| Package 1 Width | 5.10 in (12.954 cm) |
| Package 1 Length | 2.00 in (5.080 cm) |
| Package weight(Lbs) | 6.240 oz (176.901 g) |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 13.00 in (33.020 cm) |
| Package 2 Width | 13.00 in (33.020 cm) |
| Package 2 Length | 16.50 in (41.910 cm) |
| Package 2 Weight | 9.879 lb(US) (4.481 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

| | |
|--|--|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | No |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number | Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d |
| REACH Regulation | REACH Declaration |
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |

Use Again

Repack and remanufacture

| | |
|-----------|----|
| Take-back | No |
|-----------|----|

Offer Marketing Illustration

Product benefits / Features

Features

Harmony 9001K



- 
Improved security thanks to finger-safe contact blocks and light modules
- 
Robustness to withstand the harshest environments
- 
Single screw Contact Block Fastening
- 
Large metal set of accessories to customize your product
- 
Automatic self-grounding operators without additional wiring

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001K

