



## Main

|                                 |                  |
|---------------------------------|------------------|
| Range of Product                | Harmony 9001SK   |
| Product or Component Type       | Push-button      |
| Device short name               | 9001SK           |
| Type of operator                | Spring return    |
| Operator profile                | Green projecting |
| Operator additional information | Without guard    |

## Complementary

|                               |                  |
|-------------------------------|------------------|
| Bezel material                | Plastic          |
| Mounting diameter             | 1.18 in (30 mm)  |
| Contacts type and composition | 1 NO             |
| Contact operation             | Standard         |
| Mechanical durability         | 5000000 cycles   |
| Device presentation           | Complete product |

## Environment

|                           |                                                                                                                |
|---------------------------|----------------------------------------------------------------------------------------------------------------|
| Standards                 | JIS C 852<br>UL 508<br>EN/IEC 60947-1<br>JIS C 4520<br>CSA C22.2 No 14<br>EN/IEC 60947-5-4<br>EN/IEC 60947-5-1 |
| IP degree of protection   | IP66                                                                                                           |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13                                                                                     |

## Ordering and shipping details

|                   |                   |
|-------------------|-------------------|
| Category          | 21429-9001 SK,SKY |
| Discount Schedule | CS1               |
| GTIN              | 785901042716      |
| Returnability     | Yes               |
| Country of origin | MX                |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 5.08 in (12.903 cm)  |
| Package 1 Width              | 2.00 in (5.08 cm)    |
| Package 1 Length             | 12.90 in (32.774 cm) |
| Package 1 Weight             | 2.40 oz (68.039 g)   |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                       |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                         |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                         |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|