

Product data sheet

Specifications



Selector switch head, Harmony 9001K, metal, long handle, black, 30mm, 3 positions, return both sides to center

9001KS52FB

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product or Component Type	Head for selector switch
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Range of Product	Harmony 9001K

Complementary

Bezel material	Metal
Cap/operator or lens colour	black
Contacts type and composition	Without contact block
Operator position information	3 positions
Operator profile	Long handle
Operator profile	1 projecting push-button
Size	30 mm
Type of operator	Spring return both sides to centre
Cap/operator or lens colour	Black
Type of operator	Spring return
Contacts type and composition	Without contact block

Environment

NEMA Degree of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
GTIN	785901035213
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nbr. of units in pkg.	1
Package 1 Height	1.81 in (4.6 cm)
Package 1 Width	2.40 in (6.1 cm)
Package 1 Length	2.99 in (7.6 cm)
Package weight(Lbs)	4.3 oz (122.5 g)

Contractual warranty

Warranty	18 months
-----------------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.