

# Product data sheet

Specifications



Disconnect switch, TeSys VLS, protruding rotary handle, screw mounting, 65x65mm, red handle, 5mm shaft

VLSH2S5R

**Product availability:** Stock - Normally stocked in distribution facility

## Main

Range	TeSys
Device short name	VLSH
Product or Component Type	Rotary handle
Range compatibility	TeSys TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 0.2...0.3 in (4...8 mm)
Marking	0 - 1

## Complementary

Fixing mode	By 4 screws
Tightening torque	20.4 lbf.in (2.3 N.m)
Base dimension	65 x 65 mm
Height	2.6 in (65 mm)
Width	2.6 in (65 mm)
Depth	2.3 in (58 mm)
Product Weight	0.159 lb(US) (0.072 kg)

## Environment

IP Degree of Protection	IP65
NEMA degree of protection	NEMA 1 NEMA 2 UL 508 NEMA 3R UL 508 NEMA 4 UL 508 NEMA 4X UL 508 NEMA 12 UL 508 NEMA 12K UL 508

## Ordering and shipping details

Category	US10CP121734
Discount Schedule	OCP1
GTIN	3606481156907
Returnability	Yes
Country of origin	IT

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.36 in (6.000 cm)
Package 1 Width	2.68 in (6.800 cm)
Package 1 Length	2.68 in (6.800 cm)
Package weight(Lbs)	2.469 oz (70.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	7.176 lb(US) (3.255 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)

## Use Again

### Repack and remanufacture

Take-back	No
-----------	----