

9001KR12U

Double-headed push-button head, Harmony 9001K, metal, flush, 7 colours choice, 30mm, 1 latching, 1 spring return, with mechanical interlocking



Main

Range of Product	Harmony 9001K
Product or Component Type	Head for double-headed push-button
Device short name	9001K
Bezel material	Metal

Complementary

Mounting diameter	1.18 in (30 mm)
Shape of signaling unit head	Octagonal
Type of operator	1 latching, 1 spring return
Operator profile	Flush 7 colours choice unmarked
Electrical shock protection class	Class II IEC 61140
Mechanical durability	5000000 cycles
Operating position	Any position
Net Weight	1.19 lb(US) (0.54 kg)

Environment

Standards	EN/IEC 60947-5-4 CSA C22.2 No 14 UL 508 JIS C 4520 EN/IEC 60947-5-1 EN/IEC 60947-1 JIS C 852
Product Certifications	NEMA UL 508
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Vibration resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock resistance	50 gn IEC 60068-2-27
IP degree of protection	IP66 IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901008910
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.43 in (29.032 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	29.03 in (73.742 cm)
Package 1 Weight	10.56 oz (299.371 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------