

Product data sheet

Characteristics

9001KR2R

Push-button head, Harmony 9001K, metal, recessed, red, 30mm, spring return



Main

| | |
|---------------------------------|----------------------|
| Range of Product | Harmony 9001K |
| Product or Component Type | Head for push-button |
| Device short name | K |
| Operator additional information | Metal guard |

Complementary

| | |
|--------------------------------|----------------------------|
| Bezel material | Metal |
| Mounting diameter | 1.18 in (30 mm) |
| Light source | Without |
| Light block supply | Without supply |
| Contacts type and composition | Without contact block |
| [Ie] rated operational current | 10 A, AC-15 10 A, DC-13 |
| Device presentation | Basic element |
| Cap/operator or lens colour | Red |
| Operator profile | Recessed |
| Type of operator | Spring return |
| Size | 30 mm |

Environment

| | |
|---------------------------|--|
| Product Certifications | CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR NEMA CE |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| | |
|-------------------|-----------------------------|
| Category | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| GTIN | 3389118040540 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.00 in (5.08 cm) |
| Package 1 Width | 2.30 in (5.842 cm) |
| Package 1 Length | 2.80 in (7.112 cm) |
| Package 1 Weight | 3.84 oz (108.862 g) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|