

Product data sheet

Specifications



Selector switch head, Harmony 9001SK, plastic, standard handle, black, 30mm, 3 positions, stay put

9001SKS42B

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product Harmony 9001SK

Product or Component Type Head for selector switch

Device short name 9001SK

Complementary

Bezel material Plastic

Mounting diameter 1.2 in (30 mm)

Operator position information 3 positions

Contacts type and composition Without contact block

Device presentation Basic element

Cap/operator or lens colour Black

Operator profile Standard handle

Type of operator Stay put

Size 30 mm

Cam profile 2

Environment

Protective treatment TC

Ambient Air Temperature for Storage -40...158 °F (-40...70 °C)

Ambient Air Temperature for Operation -13...158 °F (-25...70 °C)

Electrical shock protection class Class II conforming to IEC 61140

IP degree of protection IP66 IEC 60529

NEMA degree of protection NEMA 1/2/3/3R/4/4X/6/12/13

Product Certifications CE
UL listed file E42259 CCN NKCR
CSA LR24590 class 3211 03

Ordering and shipping details

Category US10CS121429

Discount Schedule 0CS1

GTIN 785901820925

Returnability Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.80 in (7.112 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	2.10 in (5.334 cm)
Package weight(Lbs)	2.080 oz (58.967 g)

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65 WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile No need of specific recycling operations

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001SK

