

Product data sheet

Specifications



Power Cord, C19 to CEE/7
Schuko, 2.5m



AP9875

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Product or Component Type	Power cord
Input Connection Type	Schuko CEE 7 / EU1-16P
Number of rack unit	0U
Cable length	8.2 ft (2.5 m)
Number of cables	1

Physical

Color	Black
Product Weight	0.49 lb(US) (0.22 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
permissible voltage	90...250
Max line current	16 A
Input current limits	16 A

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	1 IEC 60320 C19
Protection Type	Without circuit breaker

Conformance

Product Certifications

Environmental

Ambient Air Temperature for Operation	32...113 °F
Relative Humidity	0...95 %
Operating altitude	0...10000 ft

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0...15240 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304189404
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.01 in (5.1 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	7.99 in (20.3 cm)
Package weight(Lbs)	0.659 lb(US) (0.299 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	10.04 in (25.5 cm)
Package 2 Width	13.07 in (33.2 cm)
Package 2 Length	21.10 in (53.6 cm)
Package 2 Weight	9.9 lb(US) (4.5 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	10
Package 3 Height	56.69 in (143.99 cm)
Package 3 Width	39.37 in (100 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	9.9 lb(US) (4.5 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **70**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

SCIP Number **1cdb2fed-a06f-4574-913d-8df8e70936b2**

REACH Regulation [REACH Declaration](#)

California proposition 65
WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Halogen content performance **Product contains halogen above thresholds**

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back **No**

WEEE Label
 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.